

## DECLARATION OF COMPLIANCE

### Bannister, Utility and Churn Brushes

Product Name	Product Code	Filament	Size	Colour	DOC Material
Bannister Brush	B5103	Extra Soft	340mm	WT, BL, RD, YL, GN	PP/PBT
Bannister Brush	B5123	Soft/Medium	340mm	WT, BL, RD, YL, GN, BK, OR, PU, GY, BN, PK	PP/PBT
Bannister Brush	B5133	Medium/Stiff	340mm	WT, BL, RD, YL, GN, BK, OR, PU, GY, BN	PP/PBT
Short Utility Brush	B6122	Medium	270mm	WT, BL, RD, YL, GN	PP/PBT
Utility Brush	B6124	Medium	410mm	WT, BL, RD, YL, GN, OR, PU	PP/PBT
Utility Brush	B6132	Stiff	270mm	WT, BL, RD, YL, GN	PP/PBT
Utility Brush	B6134	Stiff	410mm	WT, BL, RD, YL, GN, OR, PU, GY, BN, PK	PP/PBT
Churn Brush	B5327	Soft Flagged	275mm	WT, BL, RD, YL, GN	PP/PBT
Churn Brush	B5627	Medium/Stiff	275mm	WT, BL, RD, YL, GN, BK, OR, PU, GY, BN, PK	PP/PBT
Extended Nose Churn Brush	B5727	Medium/Stiff	275mm	WT, BL, RD, YL, GN	PP/PBT
Rubber Edged Churn Brush	B5628	Soft/Medium	300mm	WT, BL, RD, YL, GN	PP/PBT
Rubber Edged Churn Brush - Waterfed	B5778	Soft/Medium	300mm	WT, BL, RD, YL, GN	PP/PBT

**Brush Block:** Polypropylene grade (98%) - master batch (2%); White, Blue, Red, Yellow, Green, Black, Orange, Purple, Brown, Grey and Pink.

**Filaments:** Polyester PBT (Polybutyleneterephthalate).

**Wire Staple:** Stainless steel (AISI 304).

We confirm that the above-mentioned products fulfil the requirements on materials and articles used for food contact as described in the European Regulation 10/2011/EC as amended up to and including 202/2014/EC. The master batches are furthermore in compliance with European Resolution Res AP (89) 1.

Substances used for the manufacturing of the products are all listed in Annex I of Regulation 10/2011/EC as amended up to and including 202/2014/EC. The products contain substances restricted by specific migration limits as defined in Regulation 10/2011/EC Annex I. The products have been tested for overall and specific migration according to the specifications in Regulation 10/2011/EC as amended up to and including 202/2014/EC. Both overall and specific migration limits are complied with when the products are used as specified.

The products can be used for contact with all kinds of foodstuffs at maximum 40°C for a maximum of 1 hour.

The following substances also authorised as direct food additives (dual use additives) are present in the products:

- **Ref no. 24550, Stearic Acid**
- **Ref no. 56585, Glycerol, Esters with Stearic Acid**
- **Ref no. 92080, Talc**
- **Ref no. 93440, Titanium Dioxide**
- **Ref no. 46640, BHT**

Furthermore, the various colours of injection moulded plastic contain the following dual use additives:

- **White, Blue, Yellow, Green, Purple and Grey:** TiO<sub>2</sub> and Calcium Stearate
- **Red and Orange:** TiO<sub>2</sub>, CaCO<sub>3</sub> and Calcium Stearate
- **Brown:** RiO<sub>2</sub>, Iron Oxide and Calcium Stearate

The products do not contain a functional barrier as defined in Regulation 10/2011/EC as amended up to and including 202/2014/EC

The items do not apply any danger to health or environment according to article 3 in Framework Regulation 1935/2004/EC. The items are manufactured according to Regulation 2023/2006/EC on good manufacturing practice. The items comply with current EU-legislation on plastic materials and articles intended for food contact as described in EC Regulation 10/2011/EC as amended up to and including 202/2014/EC and the Danish executive order no. 822 of 26/06/2013.

**FDA (American Food and Drug Administration):** All raw materials are in compliance with FDA-CFR 21 / Food code 2009.

**EU regulations:** Made in accordance with EU regulations; 10/2011/EC as amended up to and including 202/2014/EC, 1935/2004/EC, 2023/2006, 579/2011/EC. EU directive; 93/43/EEC.

**Glass/Fork:** Fulfil the rules to be marked with the glass/fork symbol.

**Before use:** It is recommended to clean, disinfect and/or sterilise the article before use.

**After use:** clean, disinfect (tolerates all approved disinfectants) and sterilise the article after use according to the appropriate to its intended use, using the correct chemical, concentration, time and temperature. Sterilise in an autoclave max temp. 120°C (max temp for cleaning the article 134°C).


**N.B.** This DOC is from a migration-only perspective; please be aware that the Soft Flagged bristle finish may pose a foreign body risk and as such Klipspringer does not recommend that this type of bristle finish is used in direct contact with food items. It remains the sole responsibility of the user to validate the suitability of the product for your application; Klipspringer Ltd accept no responsibility or liability.

The exporter of the products covered by this document (customs or competent governmental authorisation No. Dk/12097870) declares that, except where otherwise clearly indicated, these products are of European Community preferential origin.

*This certificate was prepared on behalf of Klipspringer Ltd and the information included is to the best of our knowledge correct at the time of writing. Klipspringer offers the information within this document as a guide only, they do not represent any guarantee of the prescribed products in the sense of the legal guarantee regulations. It is the responsibility of the end user to ensure the items purchased are suitable for the intended application.*

Supplier/Importer	Klipspringer Ltd
Address	Rynor House, Farthing Road, Ipswich, Suffolk, UK. IP1 5AP
Telephone	+44 (0) 1473 461 800
Email	sales@klipspringer.com
Website	www.klipspringer.com

**Declaration of compliance in line with Annex 4 10/2011/EC**

Sheena Britton Technical Compliance Manager Klipspringer 15-03-2021		Date of Issue	15-03-2021
		Authorised by	S. Britton
		Revision No.	003
		Revised by	S. Britton