

DECLARATION OF COMPLIANCE

Lobby Pans, Hand Pans and Hand Scoops

Product Name	Product Code	Size	Colour	Heat Tolerance	DOC Material
Hand Scoop, 250g	P6403	250g capacity, 210 x 85 x 53mm	RD, BL, YL, GN, WT, BK, OR, PU, GY, BN, PK	Max 120°C	PP
Hand Scoop, 500g	P6405	500g capacity, 77 x 105 x 43mm	RD, BL, YL, GN, WT, BK, OR, PU, GY, BN, PK	Min -30°C Max 120°C	PP
Hand Scoop, 750g	P6417	750g capacity, 125 x 185 x 70mm	RD, BL, YL, GN, WT, BK, OR, PU, GY, BN, PK	Min -30°C Max 120°C	PP
Hand Scoop, 1000g	P6421	1000g capacity, 150 x 230 x 85mm	RD, BL, YL, GN, WT, BK, OR, PU, GY, BN, PK	Min -30°C Max 120°C	PP
Heavy Duty Food Grade Hand Dustpan, 300mm	W0023	300 x 160 x 53mm (w x d x h)	RD, BL, YL, GN, WT, BK, OR, PU, GY, BN, PK	Max 120°C	PP
Heavy Duty Food Grade Hand Pan, with Hinged Lid	W0050	325 x 360 x 155mm (w x d x h)	RD, BL, YL, GN, WT, BK, OR, PU, GY, BN, PK	Max 120°C	PP
Heavy Duty Food Grade Lobby Pan, incl. 800mm Handle*	W1050	325 x 310 x 155mm (w x d x h)	RD, BL, YL, GN, WT, BK, OR, PU, GY, BN, PK	Max 120°C	PP
Transparent Measuring Jug	P4502	2 ltr	RD, BL, YL, GN, WT, BK, OR, PU, GY, BN, PK	Max 120°C	PP
Food Grade Long-Handled Dustpan, incl. 800mm Handle*	W1510	325 x 215 x 78mm (w x d x h)	RD, BL, YL, GN, WT, BK, OR, PU, GY, BN, PK	Max 120°C	PP
Food Grade hand dustpan [pan only]	W0040	300 x 160 x 53mm (w x d x h)	RD, BL, YL, GN, WT, BK, OR, PU, GY, BN, PK	Max 120°C	PP

* See DOC-F012

Material: Polypropylene grade (98%) - master batch (2%); White, Blue, Red, Yellow, Green, Black, Orange, Purple, Pink, Brown and Grey.

We confirm that the above-mentioned products fulfil the requirements on materials and articles used for food contact as described in the European Regulation 10/2011/EC as amended up to and including 202/2014/EC. The master batches are furthermore in compliance with European Resolution Res AP (89) 1.

Substances used for the manufacturing of the products are all listed in Annex I of Regulation 10/2011/EC as amended up to and including 202/2014/EC. The products contain substances restricted by specific migration limits as defined in Regulation 10/2011/EC Annex I. The products have been tested for overall and specific migration according to the specifications in Regulation 10/2011/EC as amended up to and including 202/2014/EC. Both overall and specific migration limits are complied with when the products are used as specified.

The products can be used for long term contact with all kinds of foodstuffs at maximum 40°C and can furthermore be employed for a maximum of 2 hours at a maximum of 70°C or maximum 15 minutes at a maximum of 100°C.

The following substances also authorised as direct food additives (dual use additives) are present in the products:

- Ref no. 24550, Stearic Acid

- Ref no. 56585, Glycerol, Esters with Stearic Acid
- Ref no. 92080, Talc

Furthermore, the various colours contain the following dual use additives:

- **White, Blue, Yellow, Green, Purple and Grey:** TiO₂ and Calcium Stearate
- **Red and Orange:** TiO₂, CaCO₃ and Calcium Stearate
- **Brown:** RiO₂, Iron Oxide and Calcium Stearate

The products do not contain a functional barrier as defined in Regulation 10/2011/EC as amended up to and including 202/2014/EC

The items do not apply any danger to health or environment according to article 3 in Framework Regulation 1935/2004/EC.

The items are manufactured according to Regulation 2023/2006/EC on good manufacturing practice. The items comply with current EU-legislation on plastic materials and articles intended for food contact as described in EC Regulation 10/2011/EC as amended up to and including 202/2014/EC and the Danish executive order no. 822 of 26/06/2013.

FDA (American Food and Drug Administration): All raw materials are in compliance with FDA-CFR 21 / Food code 2009.

EU Regulations: Made in accordance with EU regulations; 10/2011/EC as amended up to and including 202/2014/EC, 1935/2004/EC, 2023/2006, 579/2011/EC. EU directive; 93/43/EEC.

Glass/Fork: Fulfil the rules to be marked with the glass/fork symbol.

Before use: It is recommended to clean, disinfect and/or sterilise the article before use.


After use: Clean, disinfect (tolerates all approved disinfectants) and sterilise the article after use according to the appropriate to its intended use, using the correct chemical, concentration, time and temperature. Sterilise in an autoclave max temp. 120°C (max temp for cleaning the article 134°C).

This certificate was prepared on behalf of Klipspringer Ltd and the information included is to the best of our knowledge correct at the time of writing. Klipspringer offers the information within this document as a guide only, they do not represent any guarantee of the prescribed products in the sense of the legal guarantee regulations. It is the responsibility of the end user to ensure the items purchased are suitable for the intended application.

Supplier/Importer	Klipspringer Ltd
Address	Foxtail House, Foxtail Road, Ipswich, Suffolk, UK. IP3 9RX.
Telephone	+44 (0) 1473 461 800
Email	sales@klipspringer.com
Website	www.klipspringer.com

Declaration of compliance in line with Annex 4 10/2011/EC

Sheena Britton
Technical Compliance Manager
Klipspringer
07-05-2021



Date of Issue 27-03-2026

Authorised by S. Britton

Revision No. 002.1

Revised by K. Smith